




PRESSALIT®

Product Item number	Lift for worktop, electrically height adjustable RK1083
Product description	EAN: 5708590293790 HMI: 61268  The name INDIVO relates to the individual configuration of the products. Electric lift for freestanding worktop. For worktops from 2401 - 3000 mm. Height adjustable 300 mm. Including 2 telescopic legs, brackets, longitudinal and cross braces and switch. Pressalit recommends overhang of 400 mm at either end of worktop to allow for ease of approach in wheel-chair. Please state desired length when ordering.
Adjustability Adjustment height Product capacity Speed upwards Noise level	Height adjustable 300 mm Maximum load (evenly distributed): 100 kg including worktop. Speed up mm: 20 mm/s Speed down mm: 20 mm/s 45 dB
Materials	Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)



Product	Lift for worktop, electrically height adjustable
Item number	RK1083
Ergonomy	A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen. The height of the worktop can be quickly and easily adjusted to the given user or situation. A freestanding worktop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.
Features	Lift heights are adjusted via switches set in the edge or directly under the worktop. Operating switches can be placed anywhere. The design of the legs and feet make the table stable and secure, and ensure the lift causes minimal inconvenience to wheelchair users. The design of the lift makes it possible to use the worktop from all sides. Height adjustable over a range of 300 mm. Available for worktops of any length between 1400 mm and 3000 mm.
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak)
Power consumption (maximum load)	Power consumption by maximum load, watt: 300 W Power consumption by standby: 2 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



Product	Lift for worktop, electrically height adjustable
Item number	RK1083
Cleaning	INDIVO lift for kitchen worktop. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate. DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.



PRESSALIT®

Product	Lift for worktop, electrically height adjustable
Item number	RK1083

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®