



<b>Product</b> <b>Item number</b>	Lift for countertop, manually height adjustable RK1113
<b>Product description</b>	<p>EAN:5708590292786 HMI: 54802</p> <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Manual lift for countertop Lift for countertop, with a crank handle Including 4 brackets Lengths from 78.8"-94.5". Height adjustable 11.8". Incl. mounting kit for brick wall. Please state desired length when ordering</p>
<b>Adjustability</b> <b>Product capacity</b>	<p>Height adjustable</p> <p>Maximum load (evenly distributed): 220 lbs including countertop.</p>
<b>Materials</b> <b>Ergonomy</b> <b>Features</b>	<p>Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Crank handle: Steel Surface treatment: Brackets: Powder lacquered (grey RAL 9006)</p> <p>Kitchen countertops which can be adjusted in height using a crank handle are the budget solution for kitchens catering to both seated and standing users. These are most commonly used in kitchens which do not require frequent, daily adjustment.</p> <p>Manual lifts are adjusted in height using a crank handle. They can be used with countertops, with or without an edge. The crank handle socket can be positioned anywhere along the front edge, except under a sink or hob. Lifts can be adapted to most standard kitchen components. Lifts are available for countertops of any length between 23.6" and 118.1". Height adjustable 11.8".</p>



# PRESSALIT®

<b>Product</b>	Lift for countertop, manually height adjustable
<b>Item number</b>	RK1113
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>



# PRESSALIT®

<b>Product</b>	Lift for countertop, manually height adjustable
<b>Item number</b>	RK1113

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

## PRESSALIT®