

PRESSALIT.

Product Item number	PLUS handrail 600 mm RT102035	
	VVS: 777565335 NRF: 6317165 EAN: 5708590145914 HMI: 19083	
Colour	NBS:N13:436 Red (RAL 3003)	
Product description	PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence. PLUS handrail, diameter 33 mm, length 600 mm, for fixed mounting. The projection of 50 mm from the wall makes it easy to take hold of the rail. Inkl. wall rosette, which covers the fixings. Material: Powder-coated aluminium and plastic Excl. mounting kit.	
Product capacity	Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.	
Materials	Basic material: Aluminium	
	Surface material: Polyester lacquer	
	Cover cap: Cycoloy plastic	
Ergonomy	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.	
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.	



PRESSALIT®

	T
Product	PLUS handrail 600 mm
Item number	RT102035
Cleaning	Handrails ALU. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as
	long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%
	NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro
	The product must be wiped down with a soft rag wrung out in clear water immediate after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
	DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parmust be wiped over with a damp cloth wrung out in clear water.
Declaration of conformity	CE UK MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices. For the UK: - Medical Device Regulation (MDR) 2002 on medical devices.



PRESSALIT.

Product		
Item number		

PLUS handrail 600 mm


RT102035


Installation in different wall types

|--|

Concrete >B25


V8616 - Mounting kit, 8 screws \emptyset 5 x 50 - plugs SX8, for brick wall. Must be ordered separately.






Solid Brick >= Mz12

V8616 - Mounting kit, 8 screws \emptyset 5 x 50 - plugs SX8, for brick wall. Must be ordered separately.






Solid Sand Lime Brick >= Hlz12

V8616 - Mounting kit, 8 screws \emptyset 5 x 50 - plugs SX8, for brick wall. Must be ordered separately.






Aerated Concrete P4

V8666 - Mounting kit, 8 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.






Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood

V8616 - Mounting kit, 8 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed.

To be ordered separately.





PRESSALIT®

Product	PLUS handrail 600 mm	
Item number	RT102035	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (8 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (8 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant	
	Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	<u></u>

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com