




# PRESSALIT®

<b>Product</b>	PLUS handrail corner 762 x 475 mm
<b>Item number</b>	RT124000
<b>Colour</b>	<p>VVS:777568200  NRF:6311224  RSK:8980576  EAN:5708590146331  HMI: 25425  NBS:N13:436</p> <p>White</p>
<b>Product description</b>	<p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail corner, diameter 33 mm, reversible right/left A: 762 mm x B: 475 mm, for fixed mounting.  The projection of 50 mm from the wall makes it easy to take hold of the rail.  Inkl. wall rosette, which covers the fixings.  Material: Powder-coated aluminium and plastic.  Excl. mounting kit.</p>
<b>Product capacity</b>	<p>Maximum load: 235 kg.  When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg.  <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i></p>
<b>Materials</b>	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cyclopedia plastic</p> <p>Strap: Nylon (PA)</p>
<b>Ergonomy</b>	<p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
<b>Warranty</b>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>





# PRESSALIT®











<b>Product</b>	PLUS handrail corner 762 x 475 mm
<b>Item number</b>	RT124000
<b>Cleaning</b>	<p>Handrails ALU.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b></p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b></p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b></p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
<b>Declaration of conformity</b>	<p>CE UK MDR This product is in compliance with all relevant requirements of:</p> <p>- Regulation (EU) 2017/745 on medical devices.</p> <p><b>For the UK:</b> - Medical Device Regulation (MDR) 2002 on medical devices.</p>



PRESSALIT®









<b>Product</b>	PLUS handrail corner 762 x 475 mm
<b>Item number</b>	RT124000

## Installation in different wall types

	<b>Concrete &gt;B25</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. 
	<b>Solid Brick &gt;= Mz12</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. 
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. 
	<b>Aerated Concrete P4</b> V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6. To be ordered separately. 
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately. 



# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS handrail corner 762 x 475 mm RT124000		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

[pressalit.com](http://pressalit.com)