

PRESSALIT.

Product	PLUS handrail 1000 mm		
Item number	RT104112		
	VVS:777565512		
	NRF:6311212		
	RSK:8980555		
	EAN:5708590318691		
	HMI: 19085		
	NBS:N13:436		
Colour	Anthracite grey		
Product description	PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathro A reliable solution with many different options, which can easily lay the grounds for increased independence.		
	PLUS handrail, diameter 33 mm, length 1000 mm, for fixed mounting. The projection of 50 mm from the wall makes it easy to take hold of the rail. Inkl. wall rosette, which covers the fixings. Material: Powder-coated aluminium and plastic Excl. mounting kit.		
Product capacity	Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.		
Materials	Basic material: Aluminium		
	Surface material: Polyester lacquer		
	Cover cap: Cycoloy plastic		
Ergonomy	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.		
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a		



PRESSALIT®

Product	PLUS handrail 1000 mm
Item number	RT104112
Cleaning	Handrails ALU. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as
	long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%
	NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro
	The product must be wiped down with a soft rag wrung out in clear water immediate after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
	DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the par must be wiped over with a damp cloth wrung out in clear water.
Declaration of conformity	CE UK MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices. For the UK: - Medical Device Regulation (MDR) 2002 on medical devices.



PRESSALIT®


Product		
Item number		

PLUS handrail 1000 mm

RT104112

Installation in different wall types


Concrete >B25 V8616 - Mounting kit, 8 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
Solid Brick >= Mz12 V8616 - Mounting kit, 8 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
Solid Sand Lime Brick >= HIz12 V8616 - Mounting kit, 8 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
Aerated Concrete P4 V8666 - Mounting kit, 8 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.	



Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood $\,$

V8616 - Mounting kit, 8 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed.

To be ordered separately.





PRESSALIT®

Product	PLUS handrail 1000 mm RT104112	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (8 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (8 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	<u>!</u>

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com