




<b>Product</b> <b>Item number</b>	PLUS handrail corner with vertical grip 762 x 762 x 1090 mm RT136112
<b>Colour</b>	VVS:777568612 NRF:6311232 EAN:5708590318783 HMI: 25428 NBS:N13:436 Anthracite grey
<b>Product description</b>	 <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail combination, 33 mm, reversible right/left, A: 762 mm x B: 762 mm x C: 1090 mm, for fixed mounting.  The projection of 50 mm from the wall makes it easy to take hold of the rail.  Inkl. wall rosette, which covers the fixings.  Material: Powder-coated aluminium and plastic.  Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>
<b>Materials</b>	Basic material: Aluminium  Surface material: Polyester lacquer  Cover cap: Cycoloy plastic  Strap: Nylon (PA)
<b>Ergonomy</b>	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.













<b>Product</b>	PLUS handrail corner with vertical grip 762 x 762 x 1090 mm
<b>Item number</b>	RT136112
<b>Cleaning</b>	<p>Handrails ALU.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b></p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b></p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b></p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
<b>Declaration of conformity</b>	<p>CE UK MDR This product is in compliance with all relevant requirements of:</p> <p>- Regulation (EU) 2017/745 on medical devices.</p> <p><b>For the UK:</b> - Medical Device Regulation (MDR) 2002 on medical devices.</p>



PRESSALIT®











<b>Product</b>	PLUS handrail corner with vertical grip 762 x 762 x 1090 mm
<b>Item number</b>	RT136112

## Installation in different wall types

	<p><b>Concrete &gt;B25</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> 
	<p><b>Solid Brick &gt;= Mz12</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> 
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> 
	<p><b>Aerated Concrete P4</b></p> <p>V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p> 
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> 



# PRESSALIT®

Product Item number	PLUS handrail corner with vertical grip 762 x 762 x 1090 mm RT136112		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®