

PRESSALIT.

	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitar	Ŋ.
Product	appliances and standard mixer tap	
Item number	R8654000	
	VVS:777637320	
	NRF:7501972	
	EAN:5708590338330	
	HMI: 100174	
Colour	White	
Product description	 Pressalit offers a wide range of daycare changing tables, both free-standing and wa hung, in several sizes and models. The wall-hung tables are also available in version where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves. All types of daycare changing tables are available in versions with sanitary appliance and a choice of taps, with or without pull-out shower heads. Freestanding changing table with sanitary appliances, 800 x 1400 mm. With electric motor and transformer, height adjustable from 650 mm - 1000 mm, wit wired hand control. Molded worktop with integrated sink, incl. lever operated mixer tap, feed/waste system and 2 wire baskets. Materials: ABS plastics, synthetic acrylic and powder-lacquered steel. 	ons o ses
Adjustability	Height adjustable	
Adjustment height	350 mm	
Product capacity	Max load: 75 kg.	
Speed upwards	Speed up mm: 14 mm/s Speed down mm: 14 mm/s	
Noise level	48 dB	
Materials	Lifting unit and baskets: Powder-laquered steel. Worktop: ABS with acrylic. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant t both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.	to



PRESSALIT.

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8654000
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at a ergonomically correct height.
Features	Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap.
Mains connection (V)	230
Actuator (motor)	LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



PRESSALIT.

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8654000
Cleaning	Changing table. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as
	Interfollowing cleaning agents have been tested by rressait and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%
	NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediatel after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
Declaration of conformity	CE UK MASK-ROHS This product complies with the relevant requirements of: - Council Directive 2006/42/EC on machinery - Council Directive 2011/65/EC on RoHS. For the UK: - The Supply of Machinery (Safety) Regulations 2008 - Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012



_

PRESSALIT

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
ltem number	R8654000

pressalit.com

Pressalit A/S Pressalitvej 1 DK-8680 Ry Tel.: +45 8788 8788 Fax: +45 8788 8789 E-mail: pressalit@pressalit.com