

PRESSALIT®

I	
Product	Lift for countertop, electrically height adjustable
Item number	RK1081-93
	EAN:5708590301365
Product description	The name INDIVO relates to the individual configuration of the products. Electric lift for freestanding countertop. For countertops from 55.1" - 78.7". Height adjustable 11.8". Including 2 telescopic legs, longitudinal and cross braces and switch. Pressalit recommends overhang of 7.9" at either end to allow ease of approach in wheel-chair. Please state desired length when ordering.
Adjustability	Height adjustable
Adjustment height	11,82 inch
Product capacity	Maximum load (evenly distributed): 220 lbs including countertop.
Speed up	Speed up: 0,79 inch/s Speed down: 0,79 inch/s
Noise level	45 dB
Materials	Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)



PRESSALIT.

Product	Lift for countertop, electrically height adjustable
Item number	RK1081-93
Ergonomy	A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen. The height of the countertop can be quickly and easily adjusted to the given user o situation. A freestanding countertop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.
Features	Lift heights are adjusted via switches set in the edge or directly under the countertor. Operating switches can be placed anywhere. The design of the legs and feet make the table stable and secure, and ensure the I causes minimal inconvenience to wheelchair users. The design of the lift makes it possible to use the countertop from all sides. Height adjustable over a range of 11.8". Available for countertops of any length between 55.1" and 11.8".
Mains connection (V)	120
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD4 (Linak) IP22
Power consumption (maximum load)	Power consumption by maximum load: 300 W Power consumption by standby: 2 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



PRESSALIT.

Product	Lift for countertop, electrically height adjustable
Item number	RK1081-93
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200

The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.

DECALCIFICATION OF ALUMINUM PARTS:

Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.



PRESSALIT®

Product	Lift for countertop, electrically height adjustable
Item number	RK1081-93

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com